

Description

TH997 is a pale blue, highly filled soft silicone rubber system suitable for used as thermal interface material of electronic devices. This silicone thermal pad is soft and flexible, and yet provides high thermal conductivity, good high temperature resistance and good electrical insulation.

Features

- Both side natural tack
- Low shore A hardness
- High compressible
- Good thermal conductivity
- Electrically insulation
- Easy to assemble

Applications

- Thermal conductive interface material for electronic parts and devices.

Cured Properties	Typical Value	Unit	Test Method
Color	Light blue	-	PEN 10
Surface tackiness	Natural tack	-	PEN 10
Density	1.58	g/cm ³	PEN 14
Hardness	15	Shore A	ASTM D2240
Thermal conductivity	1.6	W/mK	ASTM D5470
Thermal resistance			
1) 100kPa	11.7	K-cm ² /W	ASTM D5470-17
2) 300kPa	9.0	K-cm ² /W	ASTM D5470-17
3) 500kPa	7.6	K-cm ² /W	ASTM D5470-17
Tensile strength	4.8	kgf/cm ²	ASTM D412-98a
Elongation at break	91	%	ASTM D412-98a
Dielectric breakdown voltage	27.3	kV	ASTM D149-09
Dielectric strength	18.2	kV/mm	ASTM D149-09
Volume resistivity	1.9 x 10 ¹³	Ohm-cm	PEN 65
Operating temperature	-40 to 200	°C	PEN 92
Flammability	V-0	-	PEN 55


* The values above are tested based on batch to batch basis. These values are not use as a basis for preparing specifications.

* PEN is referring to Penchem standard test method, ASTM is for Test reference only.

* Specimen dimension for thermal conductivity and thermal resistance measurement – 1.0mm thickness, diameter – 3.3cm

* Specimen dimension for tensile and elongation at break test –ASTM D412 Type D dumbbell shape

Compression deflection



Revision 05: 29-Sep-2021 (TC)

Penchem Technologies Sdn Bhd (767120-A)

Address: 1015, Jalan Perindustrian Bukit Minyak 7, Kawasan Perindustrian Bukit Minyak, Mk.13, 14100 Penang, Malaysia.

Tel: +604-501 5976, 77, 78

Email: enquiry@penchem.com

Fax: +604-501 5979

Website: www.penchem.com




Management System
ISO 9001:2015
ISO 14001:2015
IATF 16949:2016
www.tuv.com
ID: 9105064144

Compression rate (%)		0	10	30	50
Initial pressure	psi	0	23.6	43.25	75.79
Sustained pressure (after 30s)	psi	0	7.93	24.22	40.03

Remark: Specimen dimension: 25mm x 25mm x 1.5mm

Compression deflection after aging test



Compression rate (%)		10	30	50
Initial	psi	6.73	21.61	43.95
125°C/500hrs	psi	8.30	26.11	50.33

Remark: Pressure were measured after sustained for 30s. Specimen dimension: 25mm x 25mm x 1.0mm

Guideline of Use

1. Pick up silicone thermal pad from release film gently
2. Make sure the surface of the substrate is clean and dried before apply the silicone thermal pad
3. Position the silicone thermal pad to substrate
4. The silicone thermal pad can be applied and removed easily (care must be taken during installation to avoid tearing and contamination).

Storage & Shelf Life

Store the silicone thermal pad in a dried place. Avoid prolong exposure to sunlight.

Shelf life: 3 years

Product Dimension

- Thickness range: 0.5 to 5.0mm

Other product dimension enquiry, please contact our sales department.

Environment, Health & Safety

This product is intended for industrial use only. For more safety information, please refer to Product Safety Data Sheet (SDS).

General Information

All right reserved. This information in this document is subjected to change without notice.

Revision 05: 29-Sep-2021 (TC)

Penchem Technologies Sdn Bhd (767120-A)

Address: 1015, Jalan Perindustrian Bukit Minyak 7, Kawasan Perindustrian Bukit Minyak, Mk.13, 14100 Penang, Malaysia.

Tel: +604-501 5976, 77, 78

Email: enquiry@penchem.com

Fax: +604-501 5979

Website: www.penchem.com



Revision 05: 29-Sep-2021 (TC)

Penchem Technologies Sdn Bhd (767120-A)

Address: 1015, Jalan Perindustrian Bukit Minyak 7, Kawasan Perindustrian Bukit Minyak, Mk.13,
14100 Penang, Malaysia.

Tel: +604-501 5976, 77, 78

Fax: +604-501 5979

Email: enquiry@penchem.com

Website: www.penchem.com



Management
System
ISO 9001:2015
ISO 14001:2015
IATF 16949:2016
www.tuv.com
ID: 9105064144